





Model: GDL125-30-18Z/7.5
Voltage: 220V
Power: 7.5kw
Current: 26.0A
Frequency: 600Hz
Rotational Speed: 18000rpm
Number of Pole: 4P
Phase: 3
Rotation Direction: Counterclockwise viewed from the end of spindle extension
Tool Holder: BT30 (Parfaite recommended)
Pop-rivet: BT30-45° (Parfaite recommended)
Weight: 34KG



- 1:Power line: Tricolor lines connected to U,V, W/ yellow-green line connected to ground
Temperature control line: two-phase of 110℃ thermistor connected to temperature protector
2:Cooling water outlet: (End 2 and 7 are connected with 8/6 hose)
3:Air return: 0.4-0.7MPa (6/4 hose)
4:Tool changing and dust-removing: 0.3-0.4MPa(6/4 hose)
5:Air seal: 0.1-0.2MPa(6/4 hose)
6:Encoder: reserved interface (no encoder for this model)
7:Cooling water inlet: delivery of water pump head 12m (Don't connect wrong!)
8:Quantity of proximity switches: Two NPN(normally open)N.O. for tool-mounting and tool-removing
Connection of proximity switch Brown line connected to +24VDC ,and blue line connected to 0VDC
Signal loading end connected to +24VDC/ the other end connected to black line
9:Air inlet while tool removing: 0.4-0.7MPa(6/4 hose)
10:Hanging ring: applied for mounting

Parameters of PTC three-core thermistor		
DC Power Supply	MaximumDC25V/100mA	
-20~25℃	≤300Ω	
≤90℃	≤750Ω	
105℃	≤1650Ω	
110℃	Rated function temperature	
115℃	≥3990Ω	
≥125℃	≥12KΩ	
≤160℃	Maximum storage temperature	

Special warning:

- 1.The spindle shall be mounted to the clamping position;otherwise it would damage the bearing!
- 2.It shall not change tools before complete stop of spindle.The manual tool-changing button shall be unavailable while spindle is rotating;otherwise it would cause the block of spindle!
- 3.The spindle can only be started after air return for air cylinder (piston reset), otherwise, it may cause the spindle stucked!
- 4.It shall ensure the dedusting air circuit is open to prevent dust or foreign materials from entering the spindle while changing tools!
- 5.The air seal shall be kept normally open!
- 6.The compressed air shall be clean and dry with filtering precision of 0.1 μm! Air sealing shall be normally open.It is recommended to apply two levels of filtering with precisions of 0.5μm/0.1μm, and the filter shall be equipped with automatic drainage.
- 7.During the operation, the frequency converter shall be set strictly according to the U-f curve of the spindle

						General cylinder				Jiangsu HQD Spindle Motor Co., Ltd.							
														Profile drawing			
标记	处数	分 区	更改文件号	签 名	年、月、日					GDL125-30-18Z/7.5-4							
设 计			标准化			阶段标记		重量	比例								
						A								1:2			
审 核																	
工 艺			批 准			共 1 张 第 1 张											

备 (通) 用 件 登 记	
田底图号	
底图号	
签 字	
日 期	
档案员	日 期